Part Number : 901560146
Product Description : 2.54mm Pitch C-Grid III Crimp Housing Single Row, 6 Circuits, Black
Series Number : 90156
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

901560146_sd.pdf

PK-90156-0001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

901190001-AS-000.pdf

PS-99020-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate per D(2025)7771-DC (04 Feb 2026) SCIP:99a2ac41-7de5-4608-9090-a7ed5f9bf3a7
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	90156
Description	2.54mm Pitch C-Grid III Crimp Housing Single Row, 6 Circuits, Black
Application	Wire-to-Board
Component Type	Receptacle
Product Name	C-Grid III
UPC	800753668058

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	PPO

Downloaded from Arrow.com.

Net Weight	0.512/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-55° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid III Vertical Single Row Headers	90120
C-Grid III Single Row Headers	90136
C-Grid III Right-Angle Single Row Headers	90121

Use with Part(s)

Description	Part Number
Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black	797582022
Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black	797582023
C-Grid III Female Crimp Terminals	90119

Downloaded from Arrow.com.