

Plugs – male fittings

COMPATIBLE FITTINGS

HE	Fittings				◆ Recommended	HE8C P/N	Central fittings	Contacts		Description
	for contacts		pin							
	socket									
	127	HE8C	127	HE8C				S	P	
804	A	101	J	101		102		T		Codable. Unlockable Daughter board FREE PLUG
801	A	101	J	101		102		YC	YC	
807	A	101	A	101		102		YL	YL	
804	PA	102	PC	102		102		T		Uncodable. Unlockable Daughter or extension board FREE PLUG
801	PA	102	PC	102		102		YC	YC	
807	PA	102	PA	102		102		YL	YL	
804	H	107				105		U	U	Codable. Unlockable. Surface mount daughter board offset from centerline, FREE PLUG
804	N	106	N	106		104		U	U	
801	N	115	N	115		114				
804	V	104	V	104		104		U	U	Codable. Unlockable Daughter board aligned with centerline, FREE PLUG
801	V	114	V	114		114				
804	E	110	R	110		113		W3	W3	
801	E	117	R	117		129		Z,Y	ZC	Codable. Unlockable For chassis or mother board (board/board, board/chassis)
807	E	117	E	117		129		YD,X1	Y,X	
804	T	111	T	111		113		W3	W3	
801	T	118	T	118		129		Z,Y	ZC	Uncodable Unlockable
807	T	118	T	118		129		YD,X1	Y,X	
804	D	103	S	103		102		T		
801	D	103	S	103		102		YC	YC	Uncodable Lockable on receptacle side Daughter board FREE PLUG
807	D	103	D	103		102		YL	YL	
804	NF	108	NF	108		104		U	U	
801	NF	116	NF	11		114				Lockable on receptacle side Surface mount daughter board aligned with centerline
804	EF	112	RF	112		113		W3	W3	
801	EF	119	RF	119		129		Z,Y	ZC	
807	EF	119	EF	119		129		YD,X1	Y,X	Uncodable Lockable on receptacle side For chassis or mother board
804	AS	124	JS	124		102		T		
801	AS	124	JS	124		102		YC	YC	
807	AS	124	AS	124		102		YL	YL	Codable Lockable on receptacle side Daughter board FREE PLUG
804	NS	126	NS	126		104		U	U	
801	NS		NS			114				
804	ES	125	RS	125		113		W3	W3	Codable Lockable on receptacle side For chassis or mother board
801	ES	125	RS	125		129		Z,Y	ZC	
807	ES	125	ES	125		129		YD,X1	Y,X	
804	ET	327	RT	327		313		W3	W3	Codable Quarter turn lockable Cable/card or cable/chassis
801	ET	327	RT	327		329		Z	ZC	
807	ET	327	ET	327		329		X1	X	

Fittings (for connectors ordered without fitting: XL or X)

Fitting	HE 8 C	101
---------	--------	-----

Fitting type

1XX: male for plug - nickel plated brass

2XX: female for receptacle – nickel plated brass

3XX: male for plug – stainless steel

4XX: female for receptacle – stainless steel

For XX, please refer to charts on pages 4 and 5 (HE8C P/N)