

Part Number : [1502010003](#)

Product Description : Ditto Hermaphroditic Crimp Housing, Positive Lock, 3 Circuit, Glow-Wire Capable, Natural

Series Number : 150201

Status : Obsolete

Product Category : Connector Housings



Documents and Resources

[1502010003 stp.zip](#)


Specifications

[1501700000-AS-000.pdf](#)

[TS-150170-0000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	150201
Description	Ditto Hermaphroditic Crimp Housing, Positive Lock, 3 Circuit, Glow-Wire Capable, Natural
Application	Power, Wire-to-Wire
Product Name	Ditto
UPC	889056215749

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	3
Color - Resin	Natural (White)
Flammability	94V-2
Gender	Hermaphroditic
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.030/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm

Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +80°C, See Product Specification

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Housings	<u>150201</u>

Use with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Terminal, Tin Brass, Preplated Tin, 22-20 AWG	<u>1502000001</u>
Ditto Hermaphroditic Crimp Terminal, Tin Brass, Preplated Tin, 26-24 AWG	<u>1502000002</u>
Ditto Terminal Position Assurance (TPA), 3.00mm Pitch, 3 Circuits, Glow-Wire Capable, Black	<u>1502130003</u>

This document was generated on Apr 28, 2026