DO NOT SCALE
DIMENSIONS IN INCH

INCH

THIRD ANGLE PROJECTION



| QTY | NUMBER | NAME | STUD SIZE | ITEM |
|---|---|---|---|---|
| 50 | 9-160313-2 | 1,0-2,5mm² FASTON REC. | - | 20 |
| 1 | 165135-0 | CASE | - | 19 |
| 50 | 130625-0 | 2,7-6,6mm² SPADE | M6 | 18 |
| 50 | 165049-0 | 2,7-6,6mm² WIRE PIN | - | 17 |
| 50 | 130094-0 | 1,0-2,6mm² RINGTONGUE | M5 | 16 |
| 50 | 165046-0 | 1,0-2,6mm² WIRE PIN | - | 15 |
| 50 | 160298-0 | 2,7-6,6mm² RINGTONGUE | M8 | 14 |
| ~~3~~ | ~~165348-0~~ | ~~PARTITION~~ | | ~~13~~ |
| 50 | 320565-0 | 1,0-2,6mm² RINGTONGUE | M4 | 12 |
| 50 | 165034-0 | 2,7-6,6mm² RINGTONGUE | M6 | 11 |
| 50 | 34072-0 | 2,7-6,6mm² PG BUTT SPLICE | - | 10 |
| 50 | 34071-0 | 1,0-2,6mm² PG BUTT SPLICE | - | 9 |
| 50 | 34070-0 | 0,25-1,6mm² PG BUTT SPLICE | - | 8 |
| 50 | 130517-0 | 0,25-1,6mm² SPADE | M4 | 7 |
| 50 | 320861-0 | 1,0-2,6mm² SPADE | M3,5 | 6 |
| 50 | 321233-0 | 1,0-2,6mm² SPADE | M4 | 5 |
| 50 | 165142-0 | 0,25-1,6mm² WIRE PIN | - | 4 |
| 50 | 9-160402-2 | 1,0-2,6mm² WIRE PIN | - | 3 |
| 50 | 31890-0 | 0,25-1,6mm² RINGTONGUE | M4 | 2 |
| 50 | 36150-0 | 0,25-1,6mm² RINGTONGUE | M3,5 | 1 |

| LTR. | REVISION RECORD | DR. | CHK. | DATE |
|---|---|---|---|---|
| - | - | - | - | - |
| - | - | - | - | - |
| - | - | - | - | - |
| - | - | - | - | - |
| - | - | - | - | - |
| - | - | - | - | - |
| B | EH-0921-96 | JvL | AB | 01-08-96 |

CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED

© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
~~RELEASED FOR PUBLICATION ,19~~

AMP

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME

# REPAIR KIT P.I.D.G.

| DR.: J.v.LIEMPT | CHK.: A. BIJNEN | APP.: - | DWG.No. 165154 | | REV.LTR. B | SHEET 1 OF 1 | A4 |
|---|---|---|---|---|---|---|---|
| DATE: 01 AUG 1996 | DATE: - | DATE: - | | | | | |

Downloaded from Arrow.com.