

# T-2 Slide Based LED Replacement Lamp



**Lamp**  
T-2 Slide based

LED replacement for incandescent lamps in a variety of colors and voltages.

**Base**  
ANSI #2, ANSI #5 and T5.5 Telephone slide base

Designed for quick installation and reduces overall cost due to less-frequent replacements.

**Single LED Color**  
Red, amber, green, orange, blue, white

Available with a variety of LEDs and provides low energy consumption, fast on/off cycling, low heat generation, and long operating life.

**Bi-Color LED**  
Red/Green

Low power consumption - uses up to 90% less energy than an incandescent lamp.

**Operating Voltage**  
2-60 VDC or 120VAC

Offered in a range of various bases (ANSI #2, ANSI#5, T5.5 telephone slide base) and mounts directly into industry standard socket.

**Compliance**  
RoHs, REACH

Ideal for mission critical applications and is available with built-in diffuser for wide angle viewing.

## T-2 Slide Based LED Lamp

Part Number	Description	Voltage	Base	Color	Qty	Unit Price
5SB-NWR120	T-2 Slide Base Replacement LED Lamp	120V	ANSI No. 5	Red	10	\$7.85
5SB-NWR12H	T-2 Slide Base Replacement LED Lamp	12V	ANSI No. 5	Red	10	\$6.55
5SB-NWR24H	T-2 Slide Base Replacement LED Lamp	24V	ANSI No. 5	Red	10	\$6.55
5SB-NWW120	T-2 Slide Base Replacement LED Lamp	120V	ANSI No. 5	White	10	\$7.85
5SB-NWW12H	T-2 Slide Base Replacement LED Lamp	12V	ANSI No. 5	White	10	\$6.55
5SB-NWW24H	T-2 Slide Base Replacement LED Lamp	24V	ANSI No. 5	White	10	\$6.55
5SB-NWG120	T-2 Slide Base Replacement LED Lamp	120V	ANSI No. 5	Green	10	\$7.85
5SB-NWG12H	T-2 Slide Base Replacement LED Lamp	12V	ANSI No. 5	Green	10	\$6.55
5SB-NWG24H	T-2 Slide Base Replacement LED Lamp	24V	ANSI No. 5	Green	10	\$6.55
5SB-NWA120	T-2 Slide Base Replacement LED Lamp	120V	ANSI No. 5	Amber	10	\$7.85
5SB-NWA12H	T-2 Slide Base Replacement LED Lamp	12V	ANSI No. 5	Amber	10	\$6.55
5SB-NWA24H	T-2 Slide Base Replacement LED Lamp	24V	ANSI No. 5	Amber	10	\$6.55

## Quote Number

When placing an order please reference quote number

NPI2018LEDT25SB