

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0673298000

Status:


Active

Overview:

Consumer USB Products

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right Angle, Solder Tail Length 2.00mm, Kinked Pins, PCB Thickness 1.20mm and 1.60mm, Gold (Au) Flash, Lead-Free



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-67329-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-89485 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	I/O Connectors
Series	67329
Application	Wire-to-Board
Comments	Standard Mount Type
Component Type	Receptacle
Overview	Consumer USB Products
Product Name	USB 2.0
Type	A
UPC	822350416887
Physical	
Boot Color	N/A
Circuits (Loaded)	4
Circuits (maximum)	4
Flammability	94V-0
Gender	Receptacle
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	2.025/g
Number of Rows	4
Orientation	Upright
PC Tail Length	2.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	1.40mm
Plating min - Mating	0.102µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.0A

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/01/2017 (12	
January 2017)	
Halogen-Free	
Status	
Not Low-Halogen	
Need more information on product	
environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any	
non-product compliance questions.	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

67329 Series

Mates With

USB Type A Plug

Shield Type	Full Shield
Shielded	Yes
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-67329-001-001
Product Specification	PS-89485
Sales Drawing	SD-67329-801

This document was generated on 05/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION