

SAI-M23-KSW-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Empty enclosure
Order No.	1170290000
Type	SAI-M23-KSW-L-7/12
GTIN (EAN)	4032248962242
Qty.	1 ST

SAI-M23-KSW-L-7/12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Dimensions and weights

Net weight	134 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	f34fc414-7303-481d-8a96-44b52af18999

Technical data customisable plug-in connectors

Housing main material	Copper-zinc alloy	Cable diameter, max.	12 mm
Cable diameter, min.	7 mm	Protection degree	IP67, IP69K
Plugging cycles	> 1000	Pollution severity	3
Shield connection	Yes	Temperature range of housing	-40...+125 °C

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ETIM 9.0	EC003556
ETIM 10.0	EC003556	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-24	ECLASS 11.0	27-44-02-24
ECLASS 12.0	27-44-02-24	ECLASS 13.0	27-44-02-24
ECLASS 14.0	27-44-02-24	ECLASS 15.0	27-44-02-24


SAI-M23-KSW-L-7/12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



SAI-M23-KSW-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Inserts without contacts**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Type	SAI-M23-BE-L-4/4	Version
Order No.	1995810000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248925674	
Qty.	1 ST	
Type	SAI-M23-BE-L-6	Version
Order No.	1170370000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962266	
Qty.	1 ST	
Type	SAI-M23-SE-L-4/4	Version
Order No.	1170380000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962518	
Qty.	1 ST	
Type	SAI-M23-SE-L-6	Version
Order No.	1170350000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962303	
Qty.	1 ST	