



All Products

Search by part # or keyword

Login/Register
My Account


0 Cart

Products ▾ Industries ▾ Services & Trainings ▾ Tools & Resources ▾ About TE ▾ Sustainability ▾ Shop TE Store

Cable Assemblies > RF Cable Assemblies

2081393-3 

1 m, Black Cable, 0 – 6 GHz Operating Frequency, 50 Ω, PVC, 3.3 mm Diameter, -40 – 105 °C [-40 – 105 °F]

TE Internal #: 2081393-3
TE Internal Description: CA,MATE AX F TO FA KRA F,RTK031,1000MMJacket Material: PVC
Cable Assembly Length (m): 1
Cable Color: Black
Operating Temperature Range: -40 – 105 °C
[-40 – 105 °F]
Outside Cable Diameter (mm): 3.3 Add to List |  Digital Datasheet**SHOP OUR DISTRIBUTORS** - No distributors are currently reporting inventory for this product. For additional information, please contact us.**We are here to help!**
Get in touch with our product experts.

CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

CAD Files

3D PDF

 3D_CVM_CVM_2081393-3_1.pdf

3D

Customer View Model

 ENG_CVM_CVM_2081393-3_1.3d_stp.zip

English

 ENG_CVM_CVM_2081393-3_1.2d_dxf.zip

English

 ENG_CVM_CVM_2081393-3_1.3d_igs.zip


English

Compatible Parts

Filter By Specification



Non-Stocked

[VIEW PRODUCT](#)

Non-Stocked

[VIEW PRODUCT](#)


Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RF CABLE ASSEMBLIES

2081393-3

1 m, Black Cable, 0 – 6 GHz
Operating Frequency, 50 Ω, PVC...

Non-Stocked

Jacket Material: PVC

Cable Assembly Length: 1 m

Cable Color: Black

Operating Temperature Range: -40
– 105 °C

Outside Cable Diameter: 3.3 mm

Contact Our Team – 24/7 Support

 +1 800 522 6752 Live Chat

See Support Details

Connect With Us



Access Partner Information

[Distributors](#)

Authorized Distributors & Resellers

[Suppliers](#)

Product FAQs

[Supplier Diversity](#)

Samples FAQs

[TE Store](#)

TE Store FAQs

Terms and Conditions of Sale

Samples Terms and Conditions

Get Answers Now

Select Your Preferences

 Language

English (EN)

 Ship to

United States (\$USD)