

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[L](#)

Honeywell Sensing and Control

[Search](#)

112-501BAJ-B01
 (Home : Products : Sensors » Temperature Sensors » Discrete Thermistors » 112)

[contacts](#)**narrow your search****Products**

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

new products**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)**Product Specifications**

Availability	Global
Resistance	500 Ohm
Tolerance	±20.0%
Accuracy	25 °C [77 °F]
Beta	2772
Operating Temperature	-60 °C to 300 °C [-76 °F to 572 °F]
Diameter	1.14 mm [0.045 in]
Termination Material	Platinum iridium
Lead Length	9.6 mm [0.375 in]
Time Constant in Air	4.0 s
Dissipation Constant	0.4 mW°C
Series Name	112

112 Series, large glass bead with adjacent leads, 500 Ohm resistance, ±20.0% tolerance, 25/85 BETA = 2772

Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**

[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING
 HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES
 HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site**Need help?**[Click here to contact us](#)[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)