


Standard



DDR SO-DIMM


When it comes to memory, Transcend has more technical prowess, manufacturing resources and quality control expertise than the competition, which allows us to produce the most stable and reliable memory modules in the industry. Our DDR SO-DIMMs use only the finest quality memory chips and components, and are rigorously tested for compatibility and reliability, making them suitable for use in small-format industrial computers, POS terminals, portable computers and notebooks.

Features

- JEDEC standard 2.6V $\pm$ 0.1V (400MHz) ; 2.5V $\pm$ 0.2V (333MHz/266MHz)
- Double-data-rate architecture; two data transfers per clock cycle
- Differential clock inputs (CK and /CK)
- DLL aligns DQ and DQS transitions with CLK transition
- Data I/O transactions on both edge of data strobe.
- Serial Presence Detect (SPD) with serial EEPROM
- Burst Length (2,4,8)
- Data Sequence (Sequential & Interleave)
- 100% tested for stability, compatibility and performance
- Top tier name-brand DRAM chips and materials
- JEDEC compliant PCB design ensures multi-platform compatibility



Specifications



Module Type	DDR Unbuffered SO-DIMM
Frequency	DDR-266 / DDR-333 / DDR-400
Number of Rank	1 Rank/ 2 Ranks
Number of Pin	200Pin
Capacity	128MB / 256MB / 512MB / 1GB
DRAM Configuration	16Mx16 / 32Mx8 / 32Mx16 / 64Mx8
Timing Description	2.5-3-3 / 3-3-3
Voltage	2.5V
PCB Height	1.25 Inches
Operate Temperature	0 ~ 85 °C

[See more](#)

Order Information

128MB

TS16MSD64V3G DDR 333 SO-DIMM 2.5-3-3 1Rx16

TS16MSD64V6G DDR 266 SO-DIMM 2.5-3-3 1Rx16

256MB

TS32MSD64V3G DDR 333 SO-DIMM 2.5-3-3 2Rx16

TS32MSD64V3F5 DDR 333 SO-DIMM 2.5-3-3 1Rx8

TS32MSD64V3M DDR 333 SO-DIMM 2.5-3-3 1Rx16

TS32MSD64V6F5 DDR 266 SO-DIMM 2.5-3-3 1Rx8

TS32MSD64V4F3 DDR 400 SO-DIMM 3-3-3 1Rx8

512MB

TS64MSD64V6J DDR 266 SO-DIMM 2.5-3-3 1Rx8

TS64MSD64V4J DDR 400 SO-DIMM 3-3-3 1Rx8

TS64MSD64V3J DDR 333 SO-DIMM 2.5-3-3 1Rx8

TS64MSD64V3M DDR 333 SO-DIMM 2.5-3-3 2Rx16

TS64MSD64V4J-I DDR 400 SO-DIMM 3-3-3 1Rx8 IND

1GB

TS128MSD64V4A DDR 400 SO-DIMM 3-3-3 2Rx8

TS128MSD64V3A DDR 333 SO-DIMM 2.5-3-3 2Rx8

TS128MSD64V6A DDR 266 SO-DIMM 2.5-3-3 2Rx8



Product Sheet

View or download the product sheet for detailed product and ordering information.



Support

Find drivers, manuals, FAQs, or software updates for your product.

Products

Memory Cards
USB Flash Drives
External Storage
Solid State Drives
DRAM Modules
Card Readers & Accessories
Car Video Recorders
Multimedia Products
Wireless Products
Apple Solutions
Industrial Solutions
Customized Solutions

Support

Support & Download
Product Verification
Product Registration
Compatibility
Where to Buy
Warranty Service

About Us

Company Profile
Awards
Investor Relations
Shareholder Services
Press
Green Initiatives
Careers

Follow US



Subscribe