

YAV26L43NK, Uninsulated Ring Terminal For 2/0 AWG, 1-Hole, 3/8" Stud, Nickel Plated

By Burndy

Catalog # [YAV26L43NK](#)



Uninsulated Ring Terminal For 2/0 AWG (Nickel Plated).

Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

General

Catalog Number	YAV26L43NK
Connector Type	Ring Terminal
Die Index	44
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810370612
UPC 14 Digit GTIN	00781810370612

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8

Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.27 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	0.83 in
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.48 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str	AN-2/0
Aircraft Size	
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29000

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50094161_E
Specifications - YAV26L43NK



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YAV26L43NK-SPEC-EN | REV 7/2025