



Color: ■ gray

Similar to illustration

Transformatorenklemmen Serie 711 mit CAGE CLAMP®

Die Transformatorenklemmen mit der Artikelnummer 711-136 ermöglichen eine einfache und zuverlässige Verbindung. Diese Transformatorenklemmen benötigen für den Leiteranschluss eine Abisolierlänge zwischen 9 und 10 mm . Dieses Produkt verwendet die CAGE CLAMP®-Technologie. Der zuverlässige und wartungsfreie CAGE CLAMP® Universalanschluss bietet die Möglichkeit, alle Arten von Leitern mit einer Käfigzugfeder anzuschließen, ohne, dass eine Vorbehandlung der Leiter erforderlich ist. Das Aufcrimpen von Aderendhülsen kann somit entfallen. In Breite x Höhe x Tiefe betragen die Maße (45 x 35 x 23,5) mm.

Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated surge voltage	-	8 kV	-
Rated current	-	25 A	-

Connection data

Clamping units	6	Connection 1	
Total number of potentials	6	Connection technology	CAGE CLAMP®
Number of connection types	1	Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
		Pole number	6

Physical data

Width	45 mm / 1.772 inches
Height	35 mm / 1.378 inches
Depth	23.5 mm / 0.925 inches



Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.421 MJ
Weight		20.3 g

Commercial data		
PU (SPU)		25 pcs
Packaging type		Box
Country of origin		DE
GTIN		4044918819428
Customs tariff number		85369010000

Product classification		
UNSPSC		39121410
eCl@ss 10.0		27-14-11-10
eCl@ss 9.0		27-14-11-10
ETIM 9.0		EC000398
ETIM 8.0		EC000398
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60998	NTR NL-7194
CCA DEKRA Certification B.V.	EN 60998	2160584.54
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 711-136			↓

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data			
CAD data		CAE data	
2D/3D Models 711-136		EPLAN Data Portal 711-136	↓
		ZUKEN Portal 711-136	↓