

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009524024

Status:


Active

Overview:

KK® Interconnect System - Molex

Description:

3.96mm Pitch KK Crimp Housing, Female, Friction Ramp, 2 Circuits, Natural



Series image - Reference only

Documents:	
3D Model	Product Specification PS-5239-007 (PDF)
Drawing (PDF)	Product Specification PS-5239-010 (PDF)
Product Specification PS-5239-002 (PDF)	Product Specification PS-5239-011 (PDF)
Product Specification PS-5239-004 (PDF)	Packaging Specification 52399200SPK-200 (PDF)
Product Specification PS-5239-005 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5239-006 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5239
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK
UPC	800753613935
Physical	
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	573.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	5239-02
Reference - Drawing Numbers	
Packaging Specification	52399200SPK-200
Product Specification	PS-5239-002, PS-5239-004, PS-5239-005, PS-5239-006, PS-5239-007, PS-5239-010, PS-5239-011
Sales Drawing	SD-5239-N

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5239 Series

Mates With

Right Angle PCB Header, [5274](#) [5272](#) , Vertical PCB Header [5271](#) , [5273](#)

Use With

[5168](#) Cat Ear Crimp Terminals for 22-28 AWG, [5167](#) Cat Ear Crimp Terminals for 18-24 AWG, [2478](#) Crimp Terminal, [2578](#) Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION