

OVERVIEW

Product is not recommended for new design.

FEATURES

- ESD protection for high-speed data lines to IEC 61000-4-2 (ESD) ±15kV (air) ±8kV (contact), IEC 61000-4-5 (Lightning) 5A (8/20µs), IEC 61000-4-4 (EFT) 40A (5/50ns)
- Package design optimized for high speed lines
- Flow-Through design
- Protects two or four I/O lines
- Low capacitance: 0.3pF typical (I/O to I/O)
- Low clamping voltage
- Low operating voltage: 5V
- Solid-state silicon-avalanche technology

PACKAGING

RClamp0524PTCT: Lead-Free, RoHS and WEEE Compliant, 3000 pcs.Tape & Reel

ORDER CODES

SLP2510P8

PB FREE/ROHS

[Learn More →](#)

BUY NOW

Shopping Cart

PART NUMBER

RCLAMP0524PATCT

QTY	UNIT PRICE (USD)	PRICE
Tape & Reel (TR)		
3,000	\$0.48741	\$1462.23
9,000	\$0.43679	\$3931.11
Cut Tape (CT)		
1	\$1.81000	\$1.81
10	\$1.15000	\$11.50
50	\$0.86260	\$43.13
100	\$0.76970	\$76.97
500	\$0.60658	\$303.29
0	\$0.00	\$ 0.00

REQUEST SAMPLE

ADD TO CART

Ordering functionality and fulfillment provided by Digi-Key Corporation. See terms [here](#).

SHOP FROM OUR DISTRIBUTORS

SHOP NOW

INVENTORY

PRODUCT	COUNTRY	DISTRIBUTOR	QTY	BUY
NORTH AMERICA				
RCLAMP0524PATCT	United States	Arrow Electronics	660	
RCLAMP0524PATCT	United States	Avnet	168000	
RCLAMP0524PATCT	Global	Mouser Electronics Inc.	147159	
RCLAMP0524PATCT	Global	DigiKey	104062	
RCLAMP0524PATCT	Canada	Future Electronics	51	
RCLAMP0524PATCT	Canada	Future Electronics	657000	
RCLAMP0524PATCT	United States	Newark, An Avnet Company	23100	
RCLAMP0524PBTCT	Global	Mouser Electronics Inc.	3012	
RCLAMP0524PBTCT	Global	DigiKey	2552	
RCLAMP0524PQTCT	Global	Mouser Electronics Inc.	169	
RCLAMP0524PQTCT	Global	Rochester Electronics, Inc.	26660	
RCLAMP0524PQTCT	Global	DigiKey	9758	
RCLAMP0524PQTCT	United States	Newark, An Avnet Company	6000	
ASIA				
RCLAMP0524PATCT	Hong Kong	Arrow/Components Agent Ltd.	2543	
RCLAMP0524PATCT	China	CEAC International Ltd.	111000	
RCLAMP0524PQTCT	China	CEAC International Ltd.	45000	
EUROPE				
RCLAMP0524PATCT	Germany	Avnet Silica	237000	
RCLAMP0524PATCT	England	Future Electronics - Europe	276000	
RCLAMP0524PQTCT	Global	Arrow Electronics (UK) Ltd.	669	

Resources

ALLRELATEDVIDEOSBLOGPRESS RELEASEAPPLICATION NOTES




WEBINAR

Optimizing Power Consumption in LoRa® and...



VIDEO

Protecting 24V DC Industrial Systems from...



VIDEO

ESD protection of automotive ethernet using...

Talk With Us Today

Semtech is here to help. When you have questions, our experts have answers.

Sales and Product Information

Restricted Document Portal

Support

CONTACT US

Newsletter

Get the latest on innovations, product launches, customer stories and news of wireless applications in the IoT space.

SUBSCRIBE

Sierra Wireless
LoRa
Products
Technology
Design Resources
Quality
About Semtech

QUICK LINKS
Cross Reference Search
Parametric Search
mySemtech
Blogs
Careers
Contact Us
Security

PRIVACY POLICY | TERMS & CONDITIONS | COOKIE PREFERENCES | ACCESSIBILITY | SUPPLIER RESPONSIBILITY | STATEMENT AGAINST HUMAN TRAFFICKING AND SLAVERY | © 2026 ALL RIGHTS RESERVED

Downloaded from [Arrow.com](#)