

Thermofit<sup>®</sup> Molded Parts  
Specification Control Drawing  
Limited Distribution

Part Number : 207K113  
Description : Boot, Strain Relief, Straight

NOTES

1. All dimensions are in  $\frac{\text{inches}}{\text{[millimeters]}}$
2. Dimensions appearing in table are as follows:  
a - As Supplied  
b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.





TABLE OF DIMENSIONS														
PART NUMBER	H		J		K		L		M	P	R	S	HW	LW
	Min	Max	Min	Max	Min	Max	Min	Max	Max	±10%	±5%	±5%	±20%	Min
	a	b	a	b	a	b	a	b	b	b	b	b	b	b
207K113	1.38 [35,0]	.80 [20,4]	1.38 [35,0]	.72 [18,4]	1.32 [35,0]	.75 [19,0]	1.38 [35,0]	.41 [10,5]	.10 [2,5]	1.46 [37,0]	.39 [10,0]	.83 [21,0]	.11 [2,9]	.03 [,76]

Raychem

RAYCHEM CORPORATION  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025

Revision : A  
Date : 12/15/94

Part Number : 207K113  
Description : Boot, Strain Relief, Straight

Thermofit<sup>®</sup> Molded Parts  
Specification Control Drawing  
Limited Distribution

Part Number : 207K113  
Description : Boot, Strain Relief, Straight

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-3	Polyolefin, Semi-rigid	RT-301	N/A		
-4	Polyolefin, Flexible	RT-1304	N/A		
-25	Elastomer, Fluid Resistant	RT-1325	N/A		

ORDERING INFORMATION

207KXXX -XX -XX /XXX

Base part number

Material dash number  
(See Compatability Chart)

Modification number  
(If necessary, see front of scd binder  
for a complete list)

Adhesive slash number  
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR  
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled.  
Check for the latest revision.

Raychem

RAYCHEM CORPORATION  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025

Revision : A  
Date : 12/15/94

Part Number : 207K113  
Description : Boot, Strain Relief, Straight  
CAD FILE MP94360