THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT – BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
ES	00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED FB00-0012-045	24JAN05	C.W	I.E

NOTES:

1. MATERIAL: H.S.G: GLASS-FILLED P.B.T COLOR: BLACK
   CONTACT: COPPER ALLOY
2. FINISH: CONTACT: MATTE TIN PLATE NICKEL UNDER-PLATE ALL OVER.
3. FINISH: CONTACT: GOLD PLATE 0.15-0.3um AT CONTACT AREA ZONE I
   MATTE TIN PLATE 0.1-0.3um AT CONTACT AREA ZONE II
   NICKEL UNDER-PLATE ALL OVER.
4. MATING CONN. (WIRE SIDE AWG#26-#28)
   6POS. TYPE173977-3 OR 175778-3
   8POS. TYPE173977-4 OR 175778-4
5. SPEC.: CURRENT RATING 2A MAX./PIN
6. RECOMMENDED MATING P.C.B DIMENSIONS



8POS 6POS



VIEW "B"

FINISH	POS.	PART NUMBER
3	8	292204-3
2	8	292204-2
2	6	292204-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

TOLERANCES UNLESS OTHERWISE SPECIFIED
10≥* : ±0.2
30≥*>10 : ±0.25
100≥*>30 : ±0.3
ANGLE : ±3°

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.15
1 PLC ± 0.15
2 PLC ± 0.15
3 PLC ± 0.15
4 PLC ± 0.15
ANGLES ± 1°

MATERIAL: SEE NOTES
FINISH: SEE NOTES

DWN	J.JIANG	05FEB03
CHK	S.YAO	05FEB03
APVD	T.SASAKI	05FEB03
PRODUCT SPEC	108-60024	
APPLICATION SPEC		
WEIGHT		

tyco Electronics
Tyco Electronics Corporation
Shanghai, P.R.China,200233

NAME: ASSSEMBLY (6P & 8P) FOR CT CARD EDGE CONNECTOR

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292204	–

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV B

AMP 1470-19 REV 31MAR2000

27DEC2002 11:03am FB001075 I:\wen\shanghai\Hybrid MiniSF Drawer\C292204_0.dwg

Downloaded from Arrow.com.