



FLORENTINA 12-up multiholder

- Linear multiholder with glare protection for 12 pieces of TINA/TINA2 lenses.
- Dimensions
C14445_FLORENTINA-HLD: 286 x 20 x 10 mm
C14446_FLORENTINA-SHD: 287 x 28 x 23 mm
- 3 position pins
- Fastening by either glue, screws or with additional retaining clips C14353_FLORENCE-1R-CLIP-A or C14409_FLORENCE-1R-CLIP-B
- Can be installed into aluminium profile
- For smaller LED's possibility to lower holder for 0.2 mm with PCB design

Typical FWHMs of different compatible optics

	Real spot	Smooth spot	Medium	Wide	Very Wide	Diffuser	Oval
TINA	13°	N/A	19°	41°	52°	16°	36°x16°
TINA2	14°	23°	20°	N/A	58°	16°	35°x17°



LED compatibility

	LED	C11004_ TINA2-RS	C12336_ TINA2-SS	C11005_ TINA2-XP-M	C11050_ TINA2-XP-O	C11417_ TINA2-XP-D	F10835_ TINA-XP-W	F11007_ TINA-WW-XP
Cree	XB-D	•	•	•	•	•	•	•
	XB-H	•	•	•	•	•	•	•
	XP-C	•	•	•	•	•	•	•
	XP-E	•	•	•	•	•	•	•
	XP-G	•	•	•	•	•	•	•
	XP-L	•	•	•	•	•	•	•
	XQ-E	•	•	•	•	•	•	•
Nichia	757	•	•	•	•	•	•	•
	NCS19	•	•	•	•	•	•	•
	NCSW119E	•	•	•	•	•	•	•
	NCSxx19B	•	•	•	•	•	•	•
	757DR	•	•	•	•	•	•	•
	NVS19	•	•	•	•	•	•	•
	NVSxx19A	•	•	•	•	•	•	•
	NVSxx19B	•	•	•	•	•	•	•



	LED	C11004_ TINA2-RS	C12336_ TINA2-SS	C11005_ TINA2-XP-M	C11050_ TINA2-XP-O	C11417_ TINA2-XP-D	F10835_ TINA-XP-W	F11007_ TINA-WW-XP
Osram	Duris S5	•	•	•	•	•	•	•
	Oslon Square PC	•	•	•	•	•	•	•
	Oslon Square	•	•	•	•	•	•	•
	Oslon SSL 150	•	•	•	•	•	•	•
	Oslon SSL 80	•	•	•	•	•	•	•
Philips Lumileds	Luxeon 3020	•	•	•	•	•	•	•
	LUXEON Q	•	•	•	•	•	•	•
	LUXEON Rebel	•	•	•	•	•	•	•
	LUXEON T	•	•	•	•	•	•	•
	LUXEON Z ES	•	•	•	•	•	•	•
	LUXEON Z	•	•	•	•	•	•	•
Samsung	3535H	•	•	•	•	•	•	•
Seoul	3030	•	•	•	•	•	•	•
	Z5	•	•	•	•	•	•	•
	Z5M1	•	•	•	•	•	•	•
	Z5P	•	•	•	•	•	•	•
Toshiba	TL1L2	•	•					

 Possibility to lower holder for 0.2 mm with PCB design

