


CDL4U(E)LD4*



AC/ DC voltage indicator with LED

6 mm

54 x 55.5 mm

24V~, 48 V~

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)LD4* 50

EPCDL4U 50




CA702	50
CA802	50

CA727/2	100
CA727/3	100
CA727/4	100
CA727/10	10


CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q 100

MT2 100



CDL4U(E)LD1/LD2



DC voltage indicator with LED

6 mm

54 x 55.5 mm

24 V-

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)LD1 50
CDL4U(E)LD2 50

EPCDL4U 50




CA702	50
CA802	50

CA727/2	100
CA727/3	100
CA727/4	100
CA727/10	10


CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q 100

MT2 100




LD1



LD2

CDL4U(E)L1/L2*



DC voltage indicator with LED

6 mm

54 x 55.5 mm

6 V-, 24 V-, 60 V-

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)L1* 50
CDL4U(E)L2* 50

EPCDL4U 50




CA702	50
CA802	50

CA727/2	100
CA727/3	100
CA727/4	100
CA727/10	10


CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q 100

MT2 100



L1



L2

CDL4U(O)



Electronic Component Carrier

6 mm

54 x 55.5 mm

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(O) 100

EPCDL4U 50




CA702	50
CA802	50

CA727/2	100
CA727/3	100
CA727/4	100
CA727/10	10

CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q 100

MT2 100



* Add required voltage to part number as a suffix i.e. CDL4U(E)LD5/110 is for 110V.