

34 DRAWING MADE IN THIRD ANGLE PROJECTION | 3 | 2 | 1 | LOC CM | DIST 53

THIS DRAWING IS UNPUBLISHED. | RELEASED FOR PUBLICATION , 19 .


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P	F	REVISIONS ZONE	LTR	DESCRIPTION	DATE	APPROVED
			U	ADDED -8 PER TTI-83-69	7288	KW/
			U_1	RESTORED	3/28/85	RS
✓			V	OBSOLETE -4 & -6 CM-473	3-7-86	KW/RS
			W	OBSOLETE -5 PER CM-858 OBSOLETE -7 PER CM-911	7-13-88	PH / RS
			Y	REVISED PER ECR-22-159524	25NOV22	M.J / T.S
			Z	REVISED PER ECR-22-161356	15DEC22	M.J / T.S







SECTION A-A




SECTION B-B







SECTION C-C



SECTION F-F



SECTION E-E



SECTION D-D

1 PLATED INSIDE WITH .000030 GOLD, OVER .000050 NICKEL.

4 REELED FOR MINI-APPLICATOR.

5 REELED FOR STANDARD APPLICATOR.

REVERSE REEL PART No. 5	FINISH	MATERIAL	INSULATION DIA	WIRE RANGE	PART NO 4
———	UNPLATED	.008 PH.BRZ.	.050-.115	#26-18 A.W.G	350019-8
———					
	1	.008 PH.BRZ.			350019-2
	PRE-TIN				350019-1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±—

MATERIAL: SEE TABLE

FINISH: SEE TABLE

CONTRACT NO

DR 7-13-82 D.A. SALTZER

CHK D.S. Steele 9/2/82

APPD R.E. Nolle 9/2/82

APPD

DSGN APPD

OTHER APPD

AMP | AMP INCORPORATED Harrisburg, Pa.

NAME: RECEPTACLE, M.R, .058 DIA.

SIZE B | FSCM NO 00779 | DRAWING NO 350019

SCALE ——— | SHEET ———

AMP 1470-15 REV 2-81

CUSTOMER DRAWING

Downloaded from Arrow.com.