

MB2x70/10.L4



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	MB2x70/10.L4
Product ID:	1SNA115340R0300
EAN:	3472591153408
Catalog Description:	MB 2 X 70/10.L4 Distribution Terminal Blocks
Long Description:	MB 2 X 70/10.L4 Distribution Terminal Blocks - Grey, G32, TH 35-7.5, TH 35-15 Rail.

Ordering

Color:	grey
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-G Distribution terminals
Instructions and Manuals:	1SNC160001C0207-CH-G Distribution terminals

Dimensions

Product Net Width:	103 mm
Product Net Height:	68 mm
Product Net Depth / Length:	44.2 mm
Product Net Weight:	210 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	10 mm
Connection Type:	Screw clamp
Function:	Distribution
Number of Levels:	1
Rated Impulse Withstand Voltage (U_{imp}):	8 kV
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	12 mm
Recommended Screw Driver:	5.5 mm

Tightening Torque: acc. IEC 60947-1 1.2 N·m
Manufacturer 1.4 N·m

Technical UL/CSA

Flammability According to UL94: V2

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225007U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220038E1002
Instructions and Manuals:	1SNC160001C0207-CH-G Distribution terminals
RoHS Information:	1SND230013F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC001894 - Distributor assembly terminal blocks
ETIM 5:	EC001894 - Distributor assembly terminal blocks
ETIM 6:	EC001894 - Distributor assembly terminal blocks

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	77 mm
Package Level 1 Depth / Length:	120 mm
Package Level 1 Height:	48 mm
Package Level 1 Gross Weight:	0.21 kg
Package Level 1 EAN:	3472591153408
Package Level 2 Units:	25 piece
Package Level 3 Units:	1200 piece
Product Packing Type:	Box

