Data sheet

# P BAG SET 3

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

## General ordering data

| | |
|---|---|
| Version | Tools, Accessories |
| Order No. | 2579420000 |
| Type | P BAG SET 3 |
| GTIN (EAN) | 4050118648331 |
| Qty. | 1 items |



Downloaded from Arrow.com.

# Data sheet

## P BAG SET 3

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 170 mm | Depth (inches) | 6.6929 inch |
| Height | 50 mm | Height (inches) | 1.9685 inch |
| Width | 260 mm | Width (inches) | 10.2362 inch |
| Net weight | 1188.8 g | | |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

### Technical data

| | |
|---|---|
| Description of article | Toolbag, fitted |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000181 | ETIM 9.0 | EC000181 |
| ETIM 10.0 | EC000181 | ECLASS 14.0 | 21-10-01-90 |
| ECLASS 15.0 | 21-10-01-90 | | |



Downloaded from Arrow.com.

# Data sheet

## P BAG SET 3

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Accessories

### unfitted



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

### General ordering data

| | | |
|---|---|---|
| Type | P BAG | Version |
| Order No. | 2548180000 | Tools, Accessories |
| GTIN (EAN) | 4050118557916 | |
| Qty. | 1 ST | |

### Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

### General ordering data

| | | |
|---|---|---|
| Type | KT 8 | Version |
| Order No. | 9002650000 | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163 | |
| Qty. | 1 ST | |

### Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design



Downloaded from Arrow.com.

# P BAG SET 3

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### General ordering data

| | | |
|---|---|---|
| Type | STRIPAX | Version |
| Order No. | 9005000000 | Tools, Stripping and cutting tool |
| GTIN (EAN) | 4008190072506 | |
| Qty. | 1 ST | |

### with LED Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.
- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

### General ordering data

| | | |
|---|---|---|
| Type | VT | Version |
| Order No. | 9918950000 | Testing tools, 2-pole voltage tester |
| GTIN (EAN) | 4032248405831 | |
| Qty. | 1 ST | |

### VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.
Weidmüller offers a complete line of pliers which comply with national and international testing standards.
All pliers are produced and tested according to DIN EN 60900.
The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

### General ordering data

| | | |
|---|---|---|
| Type | KBZ 160 | Version |
| Order No. | 9046280000 | Pliers |
| GTIN (EAN) | 4032248356478 | |
| Qty. | 1 ST | |



Downloaded from Arrow.com.

# P BAG SET 3

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Tools



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

### General ordering data

| | | |
|---|---|---|
| Type | STRIPPER ROUND TOP | Version |
| Order No. | 9918050000 | Sheathing strippers |
| GTIN (EAN) | 4032248359165 | |
| Qty. | 1 ST | |

### Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

### General ordering data

| | | |
|---|---|---|
| Type | SDIS SLIM 0.6X3.5X100 | Version |
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350 | thickness (A): 0.6 mm |
| Qty. | 1 ST | |



Downloaded from Arrow.com.