

Part Number : [500798001](#)

Product Description : 1.25mm Pitch, PicoBlade
Female Crimp Terminal, Tin (Sn) Plating, 28-26 AWG,
Reel

Series Number : 50079

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[500798001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[SPK-50079-001-001.pdf](#)

[510211109-PS-000.pdf](#)

[510211110-PS-000.pdf](#)

[510211111-PS-000.pdf](#)

[510211124-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50079
Description	1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	PicoBlade
UPC	195842202207

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	9.980/mg
Packaging Type	Reel

Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.04mm
Wire Size (AWG)	26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for 1.25mm Pitch PicoBlade Female Terminals, 28-26 AWG	<u>2130696200</u>
Hand Crimp Tool for 1.25mm Pitch PicoBlade Crimp Terminals, 28-26 AWG	<u>2002189700</u>

Japan

Description	Part Number
S-1 Applicator for PicoBlade Receptacle Terminals, 32-26 AWG	<u>570673700</u>

This document was generated on Oct 01, 2026