

Test plugs - MPS-MT - 0201744

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Test plugs, with solder connection up to 1 mm² conductor cross section, Color: silver

Why buy this product

- ✓ The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm diameter
- ✓ Two-piece test plug for individual plug color combinations
- ✓ The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 017918 098803
GTIN	4017918098803
Weight per Piece (excluding packing)	1.340 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Length	5 mm
Length contact range	10.85 mm
Width	5 mm
Pin diameter	2.3 mm
Note on dimensions	Length without insulating sleeve

Test plugs - MPS-MT - 0201744

Technical data

General

Color	silver
Material	silver-plated brass
Ambient temperature (operation)	-40 °C ... 125 °C
Nominal voltage U_N	60 V DC (30 V AC)
Nominal current I_N	10 A

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27440313
eCl@ss 9.0	27440313

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC002255
ETIM 5.0	EC002255
ETIM 6.0	EC002255

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121410

Test plugs - MPS-MT - 0201744

Approvals

Approvals


Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

EAC		EAC-Zulassung
-----	--	---------------

Accessories

Accessories

Insulating sleeve

Insulating sleeve - MPS-IH WH - 0201663



Insulating sleeve, Color: white

Insulating sleeve - MPS-IH RD - 0201676



Insulating sleeve, Color: red

Test plugs - MPS-MT - 0201744

Accessories

Insulating sleeve - MPS-IH BU - 0201689



Insulating sleeve, Color: blue

Insulating sleeve - MPS-IH YE - 0201692



Insulating sleeve, Color: yellow

Insulating sleeve - MPS-IH GN - 0201702



Insulating sleeve, Color: green

Insulating sleeve - MPS-IH GY - 0201728



Insulating sleeve, Color: gray

Insulating sleeve - MPS-IH BK - 0201731



Insulating sleeve, Color: black
