
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS




✔ Active

TE CONNECTIVITY (TE)

ASS'Y 2 POSN 63 SER

Timer Connector System

444230-1
TE Internal Number: 444230-1

EU RoHS Compliant
EU ELV Compliant

Connector Style Housing for female terminals

Mating Tab Width 2.8 mm [.11 in]

Connector System Wire-to-Board, Wire-to-Device

Number of Positions 2

Centerline (Pitch) 10.8 mm [.425 in]

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION —

Product Drawings

HOUSING, ASSY, 2 POSN., STD. POWER TIMER REC.
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Product Specifications

Product Specification

AMP Superseal Connectors 280/630 Series
PDF
English

AMP Superseal Connectors 280/630 Series
TIF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for female terminals
Connector System Wire-to-Board, Wire-to-Device
Sealable Yes
Hybrid Connector No
Primary Locking Feature On the terminal
Strain Relief No

Configuration Features

Number of Positions 2
Number of Rows 1

Electrical Characteristics

Nominal Voltage Architecture (V) 12
Operating Voltage (VDC) 12

Body Features

Color Black
Cable Exit Angle 180°
Body Material PA

Contact Features

Mating Tab Width 2.8 mm [.11 in]

Downloaded from Arrow.com.

Mechanical Attachment

Mounting Feature Yes
Terminal Position Assurance Yes
Polarized Yes

Housing Features

Centerline (Pitch) 10.8 mm [.425 in]

Dimensions

Width 27.6 mm [1.087 in]
Height 28.5 mm [1.122 in]
Length 34.55 mm [1.36 in]

Usage Conditions

Operating Temperature Range -40 – 80 °C [-40 – 176 °F]

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection Other
UL Flammability Rating UL 94-HB

Packaging Features

Packaging Method Bag

Other

Connector Position Assurance Capable No
Serviceable Yes

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.