




KLU125, Copper Terminal, Offset Tongue, Range Taking, 1 Hole

By Burndy
Catalog # [KLU125](#)

Offset Tongue Copper Terminal, 1-Hole, 1/4" Stud, #2-1/0 AWG
Cu, Non-Plated



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	<ul style="list-style-type: none">• 2 AWG• 1 AWG• 1/0
Conductor Size	2-1/0 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	2 AWG-1/0

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

Dimensions

Dimension - Pad Width inch	0.62
Package Height	3.250 in
Dimension - Height mm	0 mm
Package Weight	2.580 lb.
Package Length	4.500 in
Package Width	3.500 in
Dimension - L Length Overall mm	50 mm
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.26 in
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.61 in
Dimension - N inch	0.42 in
Dimension - Length Overall inch	1.98 in

Force Related

Installation Torque Recommended in-lb	50
---------------------------------------	----

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type Plated	Slot N
Sub Brand	SCRULUG
UPC	781810351390
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
Hardware Type	3/8 UNF Slotted SetScrew
UPC 14 Digit GTIN	00781810351390

Logistics

Minimum Pack Quantity	1
Pallet Quantity	15750
Carton Quantity	250

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-KLU125-SPEC-EN | REV 5/2026