Part Number : 2002186500
Product Description : Hand Crimp Tool for Nano-Fit Plug Crimp Terminals, 26-24 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

2002186500-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Nano-Fit Plug Crimp Terminals, 26-24 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Nano-Fit
Tool Type	Hand Crimp Tool
UPC	193264263905
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Physical

Net Weight	332.600/g

Applicable Parts

Description	Part Number
Nano-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 26-24 AWG	2014471200
Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, 26-24 AWG	2014471300
Nano-Fit Crimp Terminal, Male, 2.54µm Matte Tin Plating, Lubricated, 26-24 AWG	2014471400
Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, Lubricated, 26-24 AWG	2014471600

Downloaded from Arrow.com.