
RED INDICATES ORIGINAL


DASH NO	CABLES ACCOMMODATED	A DIM	B DIA	C HEX	ASSEMBLE PER
-201	M17/176-00002	1.116	.339	.255	TAI-143
-202	TWC-78-1				
-203	TWC-124-1A				
-204	10602, RAYCHEM				
-205	TWAC-78-1F2				
-206	7828D013D, RAYCHEM				
-207	83310 BELDEN	1.322	.442	.344	TAI-167
-208	202-3927 MICRODOT	1.116	.339	.255	TAI-143
-209	202-3942 MICRODOT				
-210	8451 BELDEN	1.322	.442	.344	TAI-167
-211	202-3934 MICRODOT				TAI-144
-212	2524E0114, RAYCHEM				
-213	TWC-78-2				
-214	TWC-124-2				
-215	BL-982 TIMES				
-216	BL-1242 TIMES .				
-217	GC875TM24H, GRUMMAN	1.116	.339	.255	TAI-143
-218	EPD 221888, RAYCHEM				
-219	2526D1114, RAYCHEM				
-220	GC875RR1, GRUMMAN				
-221	10614, RAYCHEM				
-222	10613, RAYCHEM				
-223	HMS2-1149, HUGHES				
-224	TWCP-124-3	1.322	.442	.344	TAI-144
-225	PS885PL, PRIME STOCK				

DASH NO	CABLES ACCOMMODATED	A DIM	B DIA	C HEX	ASSEMBLE PER
-301	GC875GC1, GRUMMAN	1.116	.339	.255	TAI-153
-302	GC875G81, GRUMMAN 5022E5111, RAYCHEM				
-303	7528A5314, RAYCHEM				
-304					
-305	M17/177-00001 295-3804 MICRODOT	1.322	.442	.344	TAI-173
-306	TRC-50-2 M17/134-00002				
-307	TRC-75-1				TAI-198
-308	TRC-75-2				TAI-173
-309	TRC-50-1	1.116	.339	.255	TAI-153

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS					310-0061	SH 1
REV	ECO	DESCRIPTION		DWN	APPROVED	DATE
K	12398	ADDED -224 & -225; SEE ECO		DBN	[illegible]	4-8-98





INCH	MM
.005	0.13
.030	0.76
.255	6.48
.339	8.61
.344	8.74
.442	11.23
.484	12.29
1.00	25.40
1.116	28.35
1.25	31.75
1.322	33.58
1.75	44.45

4 1 SHRINKABLE STRAIN RELIEF AND/OR SHRINKABLE SEALING SLEEVE SUPPLIED LOOSE AS FOLLOWS:

a. CABLE GROUPS -207, -210 & -307:

1 SHRINKABLE STRAIN RELIEF (1.00 LONG)
1 SHRINKABLE SEALING SLEEVE (1.25 LONG)

b. CABLE GROUPS -201 THROUGH -206, -208, -209, -217 THROUGH -223, -301, -302, -303 & -309

1 SHRINKABLE SEALING SLEEVE (1.25 LONG)

c. CABLE GROUPS -211 THROUGH -216, -305, -306 & -308

1 SHRINKABLE STRAIN RELIEF (1.75 LONG)

3. 4-LUG SUBMINIATURE CONCENTRIC TWINAX (4 PIECE ASSY) AND TRIAX (6 PIECE ASSY), FULL CRIMP CABLE PLUG


2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES

-207 SHOWN

6. EXAMPLE OF COMPLETE MODEL NO: PL155ACFL-201
BASIC MODEL NO — CABLE GROUP DASH NO

5. EXAMPLE OF COMPLETE PART NO: 310-0061-201
BASIC PART NO — CABLE GROUP DASH NO



RECOMMENDED
HEX CRIMP
SCALE: NONE

QTY	DESCRIPTION			PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ±.03 .XXX ±.005 ANGLES:	TROMPETER RF connectivity			PL155ACFL	
DWN	DBN	4/3/98	MATERIAL	CODE IDENT	DRAWING NO.	REV
CHK	[illegible]	4-7-98		14949	310-0061	K
ENGR						
APPR	[illegible]	4-8-98	SCALE 4/1	DATE 6-8-85	SHEET 1 OF 2	
NEXT ASSY						

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.