





55M0414-24-5 Product Details


 [Share](#)  [Print](#)  [Email](#)



 **Active**

Spec 44, Spec 55 and Spec RCW Wire and Cable

55M0414-24-5

55M0414-24-5 

TE Internal Number: 3135233001

Product Highlights [View All](#)

- Cable Type = Spec 55
- Wire Source = United Kingdom
- Cable Style = Primary
- Wire Size (AWG/CM) = 24 AWG
- Voltage Rating = 450 VAC

[Pricing & Availability](#) 

[Request Sample](#) 

[Add to My Part List](#) 

[Buy Product through Distributor](#) 


 Feedback

[Documents](#) | **[Features](#)** | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Cable Type 	Spec 55
Cable Style 	Primary


Electrical Characteristics	
Voltage Rating (VAC)	450

Dimensions	
Conductor Outer Diameter (mm [in])	0.595 [0.0234] 

Body Features	
Wire Size (AWG/CM)	24 AWG
Conductor Type	Silver-Coated High Strength Copper Alloy
Wire Color	Green
Nominal Outside Diameter (mm [in])	0.81 [0.032]
Wire Diameter (mm [in])	0.81 [0.032]

Configuration Features	
Number of Conductors	1

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Converted to comply with RoHS directive

Conditions for Usage	
Temperature Range (°C)	-65 – +200 
Wire Size - Details	24 AWG 0.21 mm², 0.00033 in², 19 x 36 AWG

Operation/Application	
Application	Light Weight

Packaging Features	
Wire Source	United Kingdom

Other	
Brand	Raychem

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

