

PC61-10



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Lateral Jumper Bars

General Information

Extended Product Type:	PC61-10
Product ID:	1SNA163311R2200
EAN:	3472591633115
Catalog Description:	PC61-10 Lateral Jumper Bars Black
Long Description:	Comb-type jumper bar, allows the connection of consecutive blocks or not by one compression clamp connection.

Ordering

Color:	Black
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Width:	56.5 mm
Product Net Height:	8 mm
Product Net Depth / Length:	16.5 mm
Product Net Weight:	5 g

Technical

Function:	Lateral Jumper Bars
Rated Current (I_n):	Main Circuit 35 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Brass/polyamide

Suitable For:	D4/6.P.T1
	D4/6.S.ADO
	D4/6.SN.ADO
	D4/6.SNT2.ADO
	D4/6.T
	D4/6.T3.P
	D4/8.S.ADO
	DR4/6
	DR4/6.1
	DR4/6.G
	DR4/6.P
	M4/6.D1
	M4/6.D2
	M4/6.D2.NC
	M4/6.D2.SB
	M4/6.D2.SNBT
	M4/6.D2.SNBT.NC
	M4/6.DD
	M4/6.DE
	M4/6.DL
	M4/6.DN
	M4/6.S
	M4/6.SB
	M4/6.SBT.4A
	M4/6.SNB
	M4/6.SNBT
	M4/6.SNBT.4A
	M4/6.SNTS
	M4/6.ST

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Classifications

Object Classification Code:	X
E-nummer:	2925360
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Gross Weight:	0.05 kg
Package Level 1 EAN:	3472591633115
Package Level 2 Units:	1500 piece

