
Part Number : 08650814
Product Description : KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Gold (Au)
Series Number : 6459
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 6459-(550)L
Packaging Alternative : 08650813 (Reel)



Documents and Resources

Drawings

008650814_sd.pdf

PK-2759-001-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-10-07-001.pdf

TS-10-07-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	6459
Description	KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Gold (Au)
Application	Signal, Wire-to-Board
Product Name	KK 254
UPC	800754227407

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.069/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.051µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size (AWG)	22, 24, 26, 28, 30

Downloaded from Arrow.com.

Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	2695

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 30-22 AWG	11030022
PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 30-22 AWG	638118200
Insertion Tool for KK 2.54mm Terminals, 30-22 AWG	638120000

Downloaded from Arrow.com.