

AB-SK - Support bracket



3025341
<https://www.phoenixcontact.com/us/products/3025341>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Support bracket for busbars



Your advantages

- For mounting SK shield connection clamps
- The AB-SK single-sided shield supports are particularly suitable for space-saving conductor connection for terminal blocks and devices with lateral cable entry

Commercial data

Item number	3025341
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE07
Product key	BE7113
Catalog page	Page 571 (C-3-2019)
GTIN	4017918138998
Weight per piece (including packing)	13.702 g
Weight per piece (excluding packing)	11.977 g
Customs tariff number	85389099
Country of origin	PL

AB-SK - Support bracket



3025341

<https://www.phoenixcontact.com/us/products/3025341>

Technical data


Product properties

Product type	Support bracket
Number of positions	1

Electrical properties

Nominal current I _N	0 A
--------------------------------	-----

Dimensions

Dimensional drawing	
Width	6.2 mm
Height	77.35 mm
Depth on NS 35/7,5	28.7 mm
Depth on NS 35/15	36.2 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

AB-SK - Support bracket


3025341

<https://www.phoenixcontact.com/us/products/3025341>



Drawings

Dimensional drawing



AB-SK - Support bracket



3025341

<https://www.phoenixcontact.com/us/products/3025341>

Classifications

ECLASS

ECLASS-13.0	27400607
-------------	----------

ETIM

ETIM 9.0	EC001166
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

AB-SK - Support bracket



3025341
<https://www.phoenixcontact.com/us/products/3025341>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com