USB-C to USB-A Adapter (M/F), 3.2 Gen 1 (5 Gbps)

MODEL NUMBER: **U428-000-F**





Connects an existing USB Type-A device or cable to the USB-C port on your smartphone, tablet, Ultrabook or computer in order to share data or charge a mobile device.

Highlights

- Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0
- Supports power output up to 3A for fast charging of mobile devices
- Fumble-free reversible USB-C plug on one end
- Backward compatible with USB 2.0 devices
- Slim design tailored for emerging trends toward smaller devices

System Requirements

- Device with USB-C port
- Device or cable with USB-A plug

Package Includes

- U428-000-F USB 3.2 Gen 1 (5 Gbps) Adapter, USB-C to USB-A M/F

Description

The U428-000-F USB 3.2 Gen 1 Adapter connects your new USB-C smartphones, tablets, Ultrabooks and computers to your existing USB-A devices or cables in order to share data or charge a mobile device. It supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps and power output up to 3A for fast charging of mobile devices. Unlike traditional USB connectors that can be attached only one way, the reversible USB-C male connector plugs into a USB port in either direction for fast, fumble-free connection every time. Nickel-plated molded end connectors and gold-plated copper contacts ensure superior conductivity and long life. Slim form supports evolving design trends toward smaller devices. Backward compatible with USB 2.0 devices.
USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features

Supports USB 3.2 Gen 1 Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0Supports power output up to 3A—perfect for fast charging most mobile devicesUses same USB-A female connector as USB 3.0 devicesBackward compatible with USB 2.0 devices

Reversible USB-C Male Connector Fumble-free reversible plug ensures fast, easy connection every timeStrong enough for tablets, laptops and other larger platforms

Premium Construction Gold-plated copper contacts and nickel-plated molded ends provide a lifetime of heavy use and superior conductivitySlim, sleek design tailored for emerging design trends toward smaller devices

Specifications

OVERVIEW	
UPC Code	037332190826
Technology	USB 3.x

Downloaded from Arrow.com.

INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.10
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Weight (lbs.)	0.02
Unit Dimensions (hwd / in.)	5.900 x 3.900 x 0.500
Unit Dimensions (hwd / cm)	0.9 x 1.84 x 2.1
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.01
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	0.34 BTU/Hr
Power Provided to Connected Device(s)	5V 3A (15W) Output
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035
Product Compliance	RoHS

Downloaded from Arrow.com.

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.