



APC NetShelter SX, Networking Rack Enclosure, 48U, Black, 2258H x 750W x 1200D mm [TAA]

AR3347

Overview

| Presentation | NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors. |
|--------------|--|
| Lead time | Usually in Stock |

Main

| Product or Component Type | Rack enclosure |
|---------------------------|--|
| Number of rack unit | 48U |
| Provided equipment | Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware |
| | Pre-installed casters Side Panels Vertical cable managers |

Physical

| Height | 88.9 in (2258 mm) | |
|----------------------------|--|--|
| Width | 29.5 in (750 mm) | |
| Depth | 47.2 in (1200 mm) | |
| Net Weight | 408.85 lb(US) (185.45 kg) | |
| Color | Black | |
| Mounting preference | No preference | |
| Mounting Mode | Not rack-mountable | |
| Maximum Mounting Depth | 37.8 in (958.9 mm) | |
| Minimum Mounting Depth | 11.0 in (279.4 mm) | |
| Rack Width | 19" | |
| Marking | 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels | |
| Permanent permissible load | 2250 lb(US) (1020.6 kg) dynamic 3750 lb(US) (1701.0 kg) static | |

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Downloaded from Arrow.com.

Standards UL 2416

UL 60950-1 EIA-310E

Ordering and shipping details

| GTIN | 731304284970 |
|-------------------|--------------|
| Country of origin | тн |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------|-----------------------------|--|
| Nbr. of units in pkg. | 1 | |
| Package 1 Height | 93.898 in (238.500 cm) | |
| Package 1 Width | 33.504 in (85.100 cm) | |
| Package 1 Length | 52.008 in (132.100 cm) | |
| Package weight(Lbs) | 458.959 lb(US) (208.180 kg) | |

Compliance

Compliance TAA
BAA via COTS

Contractual warranty

Warranty 5 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∇ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 632 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| Materials and Substances | | |
|--|--|--|
| Packaging made with recycled cardboard | No | |
| Packaging without single use plastic | No | |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| REACh Regulation | REACh Declaration | |

Use Again

| ○ Repack and remanufacture | | |
|----------------------------|--|--|
| Take-back | No | |
| WEEE Label | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |

Image of product / Alternate images

Alternative





























