

Part Number : [2026555000](#)

Product Description : 1.20mm Pitch, Pico-EZmate Slim Female Crimp Terminal, Gold over Nickel Plating 0.10µm, 30-28 AWG, Reel

Series Number : 202655

Status : Obsolete

Product Category : Crimp Terminals



Documents and Resources

Specifications


[2026540000-000.pdf](#)

Tooling Specifications

[2026550000-C00.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	202655
Description	1.20mm Pitch, Pico-EZmate Slim Female Crimp Terminal, Gold over Nickel Plating 0.10µm, 30-28 AWG, Reel
Application	Wire-to-Board
Keyword	Pico-EZmate 1.2
Product Name	Pico-EZmate Slim
UPC	191128182058

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	6.690/mg
Packaging Type	Reel
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.60-0.70mm
Wire Size (AWG)	28, 30

Wire Size mm ²	0.055-0.089
---------------------------	-------------

Mates With / Use With

Use with Part(s)

Description	Part Number
Pico-EZmate Slim Receptacle Housing, Friction Lock, 2 Circuits, Black	<u>2026542021</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 1.20 Pico-EZmate Female Crimp Terminals, 30-28 AWG	<u>2002188800</u>
FA2 Mechanical Feed Crimp Applicator for 1.20mm Pitch Pico-EZmate Slim Female Crimp Terminals, 30-28 AWG	<u>2130692700</u>

Japan

Description	Part Number
S-1 Applicator for Pico-EZmate Slim Receptacle Terminal, 30-28 AWG	<u>5781393700</u>

This document was generated on Jun 02, 2026