

AXS5MP1V 5 Pole Vertical Male Plug PCB Mount with Protective Cap, IP65, For 1.5mm to 2.0mm Panel Thickness

AXS5MP1V 5 POLE VERTICAL MALE PLUG PCB MOUNT WITH PROTECTIVE CAP, IP65, FOR 1.5MM TO 2.0MM PANEL THICKNESS

PART NUMBER: AXS5MP1V
DATASHEET: View / Download

SPECIFICATIONS:

No. of Poles: 5
Contact Type: Pin
Gender: Male
Contact Plating: Tin
Current Carrying Capacity: 7.5A
Voltage Rating: 133V
Termination: Printed Circuit Board (PCB)
Max. Wire Gauge: 18AWG
Housing Material: Thermoplastic
Finish: Black
IP Rating: IP65
Operating Temperature: -25°C to +75°C
Flammability Rating: UL94V-0
Environmental: Complies with EU RoHS 2 Directive 2011/65/EU
Mating Cycles: 1000
Mating Part(s)*: AX5F*

QUANTITY

1 + -

REQUEST A QUOTE

Like Be the first of your friends to like this.

Description

5 Pole Vertical Male Plug PCB Mount with Protective Cap, IP65, For 1.5mm to 2.0mm Panel Thickness

RELATED ITEMS



AX5F 5 Pole XLR Female Cable Connector, Nickel Finish. Comparable

REQUEST A QUOTE



AX5F0M 5 pole Socket (Female) Plug. AX XLR Audio Cable Connector. Satin

REQUEST A QUOTE



AX5FB 5 Pole Socket (Female) Plug. XLR AX Audio Cable Connector. Black

REQUEST A QUOTE



AXS5MP 5 Pole Male Plug Chassis Mount with Protective Cap, IP65,

REQUEST A QUOTE



AXS5MP1 5 Pole Male Plug Chassis Mount with Protective Cap, IP65,

REQUEST A QUOTE



AXS5MP1H 5 Pole Horizontal Male Plug PCB Mount with Protective Cap,

REQUEST A QUOTE



AXS5MP2V 5 Pole Vertical Male Plug PCB Mount with Protective Cap, IP65,

REQUEST A QUOTE



AXS5MPH 5 Pole Horizontal Male Plug PCB Mount with Protective Cap, IP65,

REQUEST A QUOTE



AXS5MPV 5 Pole Vertical Male Plug PCB Mount with Protective Cap, IP65,

REQUEST A QUOTE

Downloaded from Arrow.com.

Recently Viewed Items

TURN HISTORY OFF

Recently Viewed Items

TURN HISTORY OFF

Copyright 2025 Amphenol Sine Systems. All Rights Reserved. eCommerce Software by 3dcart.

Downloaded from Arrow.com.