

Marker carriers - CARRIER-EMP 22 (27X27) - 0827449

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker carriers, black, unlabeled, mounting type: snapped, diameter: 22 mm, lettering field size: 27 x 27 mm

Your advantages

- ✓ Snap-in UC-/US-EMP ... labels are available for marking CARRIER-EMP 22 ... marker carriers
- ✓ Can be used for all buttons and switches with 22 mm diameter

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 446563
GTIN	4046356446563
Weight per Piece (excluding packing)	1.600 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	60 mm
Width (a)	29.5 mm
Height (c)	3.2 mm
Diameter	22.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Marker carriers - CARRIER-EMP 22 (27X27) - 0827449

Technical data

General

Color	black
Components	free from silicone and halogen
Material	PA
Marking mounting type	snapped

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27144075
eCl@ss 11.0	27281105
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 9.0	27144075

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC002248
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 19.0	39131504

Marker carriers - CARRIER-EMP 22 (27X27) - 0827449

Accessories

Accessories

Device marking

Snap-in markers - UC-EMP (27X27) - 0825451




Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 27 mm, Number of individual labels: 6

Snap-in markers - UC-EMP (27X27) YE - 0825452



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 27 mm, Number of individual labels: 6

Snap-in markers - UC-EMP (27X27) SR - 0825453



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 27 mm, Number of individual labels: 6