

Door position switch - PLD E 400-DS-MS/1,0-FS/0,6 - 2702337

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Door position switch with 1 m cable with M8 plug and 0.6 m cable with M8 socket (Snap-in), including mounting accessories

Product Description

This door position switch is used to automatically switch the class 400 PLD enclosure lights on or off when opening or closing the control cabinet door. If the enclosure lights are connected in series, this door position switch is only to be used from the second light onward.

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 127460
GTIN	4055626127460
Weight per Piece (excluding packing)	160.000 g
Custom tariff number	85365080
Country of origin	Germany

Technical data

Dimensions

Width	31 mm
Height	30.5 mm
Depth	98.3 mm
Note on dimensions	Without connected cables

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Degree of protection	IP54

General

Door position switch - PLD E 400-DS-MS/1,0-FS/0,6 - 2702337

Technical data

General

Net weight	155 g
Mechanical service life	10 x 10 ⁶ cycles

Power supply for module electronics

Rated voltage	24 V DC
Rated current	3 A

Standards and Regulations


Protection class	II
------------------	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Circuit diagram



Classifications

eCl@ss

eCl@ss 5.1	27142506
eCl@ss 8.0	27119220
eCl@ss 9.0	27119290

ETIM

ETIM 5.0	EC002557
ETIM 6.0	EC002557

UNSPSC

UNSPSC 13.2	39111541
-------------	----------

Door position switch - PLD E 400-DS-MS/1,0-FS/0,6 - 2702337

Approvals




Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
cULus Listed			

Accessories

Accessories

Sensor/Actuator cable - SAC-3P-M 8MS/ 0,6-PUR/M 8SIFS - 1417699



Sensor/Actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, Cable length: 0.6 m

Sensor/Actuator cable - SAC-3P-M 8MS/ 1,0-PUR/M 8SIFS - 1417700



Sensor/Actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, Cable length: 1 m

Door position switch - PLD E 400-DS-MS/1,0-FS/0,6 - 2702337

Accessories

Sensor/Actuator cable - SAC-3P-M 8MS/ 3,0-PUR/M 8SIFS - 1417701



Sensor/Actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, on Socket straight M8 Snap-in, Cable length: 3 m

Phoenix Contact 2017 © - all rights reserved
<http://www.phoenixcontact.com>