



Part Number : [08580121](#)
Product Description : KK 396 Crimp Terminal
2478, 24-18 AWG, Reel, Phosphor Bronze,
0.51µm Selective Gold (Au)
Series Number : 2478
Status : Active
Product Category : Crimp Terminals
Engineering Number : 2478-3-(550)
Packaging Alternative : 08580122 (Bag)




Documents & Resources

Drawings
[008580121_sd.pdf](#)

Specifications
[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	2478
Description	KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au)
Application	Power, Wire-to-Board
Product Name	KK 396, KK 508
UPC	800754226967

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	0.051µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>
KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<u>11030016</u>
Terminator Die	<u>11402096</u>
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG	<u>638279500</u>
Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals, 24-18 AWG, check ATS for Wire Insulation Diameter Compatibility	<u>638885000</u>

This document was generated on Mar 14, 2025