
Part Number : 887328802
Product Description : USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 1.80m Length, Black
Series Number : 68768
Status : Obsolete
Product Category : I/O Cable Assemblies
Engineering Part Number : 887-3288-02



Obsolete

Documents and Resources

Drawings

PK-88740-012-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	I/O Cable Assemblies
Series	68768
Description	USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 1.80m Length, Black
Assembly Configuration	Dual Ended Connectors
Connector to Connector	USB Type A-to-Mini-B
Product Name	USB
UPC	800756208428

Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V

Physical

Cable Length	1.80m
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	62.000/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	4.064µm

Obsolete

Downloaded from Arrow.com.

Single Ended	No
Wire/Cable Type	Round
Wire Insulation Diameter	N/A
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini USB Vertical B-Receptacles	500075
Mini USB Right-Angle B-Receptacles	54819
Mini USB Right-Angle B-Receptacles	67503
USB Shielded I/O Type A Receptacles	67329
USB Shielded I/O Type A Upgright Right-Angle Receptacles	89485

Obsolete

Downloaded from Arrow.com.