



Menu

HOME / SUPERNANO 1200W 1U REDUNDANT POWER SUPPLY (PWS-1K21P-1R)

Feedback

IN STOCK

\$224.28

Buy 10 \$215.02/each

Buy 100 \$205.77/each

Buy 1000 \$196.51/each

• PMBus 1.2 Support for Remote Management

• Optimized for 1U Server

• 80 Plus Gold

• Supernano Certified

Qty: 1

ADD TO CART

Add to Wishlist

Add to Compare

More Views

PLEASE ENTER SKU# TO CHECK VALIDATION STATUS

SystemChassis

SKU #:

Please enter your server SKU

VALIDATION STATUS

CLEAR

i

Description

Detailed Specification

Prop 65 Warning

Description

The Supernano PWS-1K21P-1R is an 80 Plus Gold power supply capable of supplying 1200W output power with 92% efficiency. Enjoy the simplicity of active power factor correction (PFC) and automatically correct AC input for a full range of voltages. Features a card edge connector for connection with the backplane or compatible server chassis.

<https://store.supernano.com/1200w-1u-pws-1k21p-1r.html>

Downloaded from [Arrow.com](#)

1/3

Supermicro 1U systems. This power supply is designed to not only provide you reliable power to your Supermicro server but also protects it from over voltage, over current and short circuiting via protective circuitry embedded into the unit. Rest easy knowing your hardware will be up and running with a mean-time between failure (MTBF) of greater than 150,000 hours and an LED indicator to keep you informed on normal/abnormal conditions for your PSU. This power supply is redundant to safe-guard your system from power failure and allows for hot-swap replacement to eliminate system downtime. All materials contained comply with RoHS requirements and is certified by Supermicro.

Detailed Specification

TOTAL POWER OUTPUT	1000W / 1200W
TYPE	Module
TYPE OF POWER SUPPLY	Power Supply
FORM FACTOR	1U
DIMENSION (W X H X L)	76 x 40.4 x 336 mm
5V	N/A
+12V	1000W: 100-140V: 83A; 1200W:180-240: 100A
+3.3V	N/A
5V STANDBY	90 to 264Vac: 4.0 / 4.0A
INPUT VOLTAGE RANGE	1000W: 100-140V; 1200W: 180-240V
INPUT FREQUENCY RANGE	50-60Hz
INPUT CURRENT RANGE	1000W: 11.5-8A; 1200W: 8.5-5A
OUTPUT TYPE	Gold Finger
8PIN / 4PIN (12V) CONNECTOR	N/A
PFC	Yes
PMBUS	Yes
ENERGY EFFICIENCY	92% Peak
80 PLUS CERTIFICATION	80 Plus Gold
WARRANTY	1 year warranty
PRODUCT ENVIRONMENTAL COMPLIANCE	RoHS and REACH compliant, details available upon request

Prop 65 Warning

This product can expose you to chemicals including lead, known to the State of California cause cancer and birth defects or other reproductive harm. For more information, go to



COMPANY

- ABOUT US
- CONTACT US
- CONDITION OF USE
- PRIVACY POLICY

QUICK LINKS

- FAQ

ACCOUNT

- MY ACCOUNT
- RETURN POLICY
- WARRANTY POLICY

SIGN UP FOR SPECIAL OFFERS

SIGN UP

CONNECT WITH US

- FACEBOOK
- TWITTER
- YOUTUBE
- LINKEDIN
- GOOGLE+

