
SMD / SMT Inductors (Coils)

NL453232T-220J-PF

Product Status	Obsolete Recommended Alternate Part No. : NLV32T-220J-EF (Interchangeability is not guaranteed.) Discontinue Issue Date : May.28, 2020 Last Purchase Order Date : Mar.31, 2022 Last Shipment Date : Sep.30, 2022
Applications	Commercial Grade
Feature	No DirectivityNo Directivity Wire WoundWire Wound Ferrite CoreFerrite Core
Series | Type	NL453232
Brand	TDK
Environmental Compliance	RoHS



Size	
Length(L)	4.50mm ±0.30mm
Width(W)	3.20mm ±0.20mm
Thickness | Height	3.20mm ±0.20mm
Recommended Land Pattern (A)	1.50mm Nom.
Recommended Land Pattern (B)	3.00mm Nom.
Recommended Land Pattern (C)	2.80mm Nom.

Electrical Characteristics	
Inductance	22µH ±5% at 2.52MHz
Rated Current	180mA
DC Resistance [Typ.]	
DC Resistance [Max.]	3.2Ω
Self Resonant Frequency [Min.]	13MHz
Self Resonant Frequency [Typ.]	
Q [Min.]	50 at 2.52MHz
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 85°C (Including Self-Temp. Rise)
Soldering Method	Wave (Flow) Reflow Iron Soldering
AEC-Q200	NO

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

SMD / SMT Inductors (Coils)

NL453232T-220J-PF


Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	500pcs
Weight	0.18g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.


Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)

Impedance




NL453232T-220J-PF

Rac




NL453232T-220J-PF

Inductance




NL453232T-220J-PF

Q




NL453232T-220J-PF

DC Bias Characteristic



NL453232T-220J-PF (Amb. Temp. = 20 °C)

Temperature Characteristic



NL453232T-220J-PF(No Bias) NL453232T-220J-PF(DC Bias = 0.09A)

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.


Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

SMD / SMT Inductors (Coils)


NL453232T-220J-PF

Associated Images

Shapes and Dimensions



Land Pattern (Terminal Connection)



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.