

RIHE-1611-N/P-IN-48VAC/DC



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → PLC Wiring Systems
→ PLC Decoupling Interfaces

General Information

Extended Product Type:	RIHE-1611-N/P-IN-48VAC/DC
Product ID:	1SNA020957R2200
EAN:	3472590209571
Catalog Description:	RIHE-1611-N/P-IN-48VAC/DC - Decoupling Interface
Long Description:	RIHE 16N/P relay 1NO 5 A input interface 48 V AC/DC for HE10/20.

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85371098

Popular Downloads

Data Sheet, Technical Information:	1SNC127006C0202
Instructions and Manuals:	1SNC127006C0202

Dimensions

Product Net Width:	165 mm
Product Net Height:	75 mm
Product Net Depth / Length:	65 mm
Product Net Weight:	0.208 kg

Technical

Connection Type:	Pluggable - Screw clamp
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	7.5 mm
Recommended Screw Driver:	3.5 mm

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 14 AWG
Flammability According to UL94:	V0

Certificates and Declarations (Document Number)

cUL Certificate:	1SND117003A0201
-------------------------	-----------------

Declaration of Conformity - CE:	1SND225028U1000
Environmental Information:	1SNC127006C0202
Instructions and Manuals:	1SNC127006C0202

Classifications

Object Classification Code:	K
ETIM 4:	EC001437 - Switching relay
ETIM 5:	EC001437 - Switching relay
ETIM 6:	EC001437 - Switching relay

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	135 mm
Package Level 1 Depth / Length:	175 mm
Package Level 1 Height:	74 mm
Package Level 1 Gross Weight:	0.208 kg
Package Level 1 EAN:	3472590209571
Package Level 2 Units:	16 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Package Level 3 Units:	384 piece
Product Packing Type:	Box

