



Part Number : [638116500](#)
Product Description : PremiumGrade Hand Crimp Tool for SPOX Terminals, 18-24 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

- [Commercial Crimp Book TM-638000029-001.pdf](#)
- [Commercial Crimp Book TM-638000029VN-001.pdf](#)
- [Commercial Crimp Book TM-638000029RU-001.pdf](#)
- [Commercial Crimp Book TM-638000029JP-001.pdf](#)
- [Commercial Crimp Book TM-638000029FR-001.pdf](#)
- [Commercial Crimp Book TM-638000029SK-001.pdf](#)
- [Commercial Crimp Book TM-638000029TH-001.pdf](#)
- [Commercial Crimp Book TM-638000029KR-001.pdf](#)
- [Commercial Crimp Book TM-638000029DE-001.pdf](#)
- [Commercial Crimp Book TM-638000029PL-001.pdf](#)
- [Commercial Crimp Book TM-638000029TW-001.pdf](#)
- [Commercial Crimp Book TM-638000029IT-001.pdf](#)
- [Commercial Crimp Book TM-638000029CN-001.pdf](#)
- [Commercial Crimp Book TM-638000029MY-001.pdf](#)
- [Commercial Crimp Book TM-638000029SP-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for SPOX Terminals, 18-24 AWG
Comments	See Tooling Specification (PDF) Above; Type: 2C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Family	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822350700573

Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling").</p> <p>When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer.</p> <p>Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
---------------------	--

Physical

Net Weight	576.034/g
------------	-----------

Applicable Parts

Global

Description	Part Number
SPOX Crimp Terminal, 18-24 AWG, Brass, Bag	<u>0008701030</u>
SPOX Crimp Terminal, 18-24 AWG, Phosphor Bronze, Bag	<u>0039000022</u>
SPOX Crimp Terminal, 18-24 AWG, Brass, Reel	<u>0008701031</u>
SPOX Crimp Terminal, 18-24 AWG, Phosphor Bronze, Reel	<u>0039000021</u>

This document was generated on Aug 22, 2023