

Specification Sheet


Part Number: 553-50002

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, 0.125" (3.17mm), PO-X, White, 250/box

Article Number 553-50002

Type HST3-1WH

Color White (WH)

Quantity Per pack

Product Description HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

Short Description ShrinkTrak Labels, 1-Sided, Unslit, 0.125" (3.17mm), PO-X, White, 250/box

Global Part Name HST3-1WH-PO-X-WH

Variant Thin-Wall

Width W (Imperial) 1.9

Width W (Metric) 48.26

Thickness T (Imperial) .003

Thickness T (Metric) .0762

Height H (Imperial) 0.235

Height H (Metric) 5.69

Width of Liner (Metric) 76.2

Width of Liner (Imperial) 3.0

Outside Diameter OD (Imperial) 0.125

Outside Diameter OD (Metric) 3.2

Outside Diameter Max (Imperial) 0.125

Outside Diameter Max (Metric) 3.2

Wall Thickness WT (Imperial) 0.031

Wall Thickness WT (Metric) 0.79

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AS81531 MIL-STD-202G Method 215K SAE-AMS-DTL-23053/5 Class 1 and 3
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 224 125 °C 600V VW-1
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3917320000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)