


Data Sheet | Item Number: 711-408

Transformer fuse terminal block; for fuse 6.35 x 32 mm; CAGE CLAMP® connection for conductors; 22.5 mm wide; orange

<https://www.wago.com/711-408>

DISCONTINUED:
31.12.2024



Color: ■ orange

Similar to illustration

Transformer terminal block, 711 Series, CAGE CLAMP®

Our transformer terminal block (item number 711-408) makes connecting wires quick and easy. Ensure that the strip lengths are between 9 and 10 mm when connecting conductors to this transformer terminal block. This product features one conductor terminal and utilizes CAGE CLAMP®. Our CAGE CLAMP® connection provides a proven and maintenance-free way to connect all types of conductors. You do not need to prepare the conductor in any way, such as crimping ferrules. Dimensions: (22.5 x 57.1 x 23.5) mm (width x height x depth).

Electrical data

Ratings per	IEC/EN 60664-1		
	III	III	II
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated impulse withstand voltage	-	8 kV	-
Rated current	-	10 A	-

Connection Data

Clamping units	1
Total number of potentials	1
Number of connection types	1

Connection 1

Connection technology	CAGE CLAMP®
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data

Width	22.5 mm / 0.886 inches
Height	57.1 mm / 2.248 inches
Depth	23.5 mm / 0.925 inches

Material data

Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.278 MJ
Weight	13.1 g

Commercial data

PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918684620
Customs tariff number	85369095000
End of Sale	2024-12-31
End of Production	2025-10-01
End of Delivery	2025-11-28
End of Service and Repair	2026-12-01

Product Classification

UNSPSC	39121410
eCl@ss 10.0	27-14-11-10
eCl@ss 9.0	27-14-11-10
ETIM 9.0	EC000398
ETIM 10.0	EC000398
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 711-408



Documentation

Additional Information

Technical Section

03.04.2019

pdf

2027.26 KB



CAD/CAE-Data

CAE data

EPLAN Data Portal
711-408



WSCAD Universe
711-408

