

Data Sheet | Item Number: 249-119

Group marker carrier; gray

<https://www.wago.com/249-119>



Color: ■ gray

Technical data		
Suitable		for end stops (249-116 and 249-117); for 1 marker or self-adhesive label and transparent protective marker cover
Properties		Snap-on type and adjustable in height from 43.5 mm to 59.5 mm

Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0

Physical data		
Width		10 mm / 0.394 inches

Material data		
Color		gray
Weight		1.5 g
Fire load		0.041 MJ

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		50 (25) pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332188371
Customs tariff number		39269097900



Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-40-75
eCl@ss 9.0	27-14-40-75
ETIM 9.0	EC002248
ETIM 10.0	EC002248
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 249-119	

Documentation			
Bid Text			
249-119	19.02.2019	xml 2.79 KB	
249-119	04.01.2018	doc 24.00 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 249-119 	EPLAN Data Portal 249-119 
	WSCAD Universe 249-119 
	ZUKEN Portal 249-119 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Label



Item No.: 210-345
Labels; for laser printer; permanent adhesive; 9.5 x 25 mm; white



Item No.: 210-808
Labels; for Smart Printer; 9.5 x 25 mm; white



Item No.: 210-807
Labels; for Smart Printer; permanent adhesive; 8 x 20 mm; 3000 pieces on roll; white



Item No.: 210-708
Labels; for TP printers; 9.5 x 25 mm; white

1.1.1.2 Marker



Item No.: 209-113
Cardboard signs; for laser printer; 9.5 x 25 mm; white


1.1.1.3 Protective marker cover



Item No.: 209-114
Protection cover; transparent

Installation Notes

Application



This system can be used as an additional group marker carrier or continuous marking strip carrier for terminal strips or single-deck rail-mount terminal blocks, e.g., for:

- DIN-35 rail-mount terminal strips (264 Series)
- Single-deck rail-mount terminal blocks (279 to 284 Series) with a maximum height of 49 mm (1.93 inch) from upper-edge of DIN-rail (observe conductor radius)Receptacles for:
 - 1 x marker
 - 2 x WMB Multi marker or
 - 3 x WCB Combi marker or
 - 1 x WFB continuous marking strip