



**Part Number :** [194390007](#)

**Product Description :** Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural

**Series Number :** 19439

**Status :** Active

**Product Category :** Quick Disconnects

**Engineering Part Number :** LOCKQD V-2



---

## Documents and Resources

### Drawings

[194390007\\_sd.pdf](#)


[194390008-000.pdf](#)

### Specifications

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Quick Disconnects
Series	19439
Description	Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural
Product Name	Loxon
Style	Insulator Housing
Type	Loxon Locking Disconnect
UPC	193264611683

#### Agency

UL	E79133
----	--------

#### Electrical

Voltage - Maximum	600V AC
-------------------	---------

#### Physical

Barrel Type	N/A
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Capable	Yes
Insulated	N/A
Insulation	N/A
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.905/g
Orientation	Straight

Packaging Type	Carton
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390001</u>
Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390002</u>
Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390003</u>
Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390004</u>
Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm	<u>194390005</u>
Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Tab 6.35 x 0.81mm, Carton	<u>194390006</u>

---

This document was generated on Apr 14, 2026