

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
1. CASSETTE MODULE WEIGHT:
   2.4oz [69.0g]
2. DIMENSIONS IN BRACKETS ARE METRIC.



UNIVERSAL 12F - CASSETTE (U)												
MPO END / LC END	FIBER POSITION FROM MPO END TO LC END											
MPO POSITION	1	2	3	4	5	6	7	8	9	10	11	12
LC POSITION	12	1	11	2	10	3	9	4	8	5	7	6

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01C	8/12/21	JSP	JGD	EJH	C. CORRECTED FIBER TABLE B. ADDED OM5 CASSETTES	M02947YB-DC
01B	05-30-19	SAT	DWW	EJH	A. ADDED P/N FQ9N-12-LAU.	M02947YB-DC
01A	06-28-18	SAT	JGD	EJH	RELEASED TO PRODUCTION	M02947YB-DC

TITLE

QUICKNET SFQ CASSETTE, 12 FIBER DUPLEX
LC TO MPO CASSETTE METHOD U [UNIVERSAL]

CUSTOMER DRAWING

ITEM REVISION NAME: M02947YB/01

DATASET FILE NAME: M02947YB_DC/01C

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [0.3]
.XX ± .03 [0.8] ANGLES ±

THIRD ANGLE PROJECTION

PANDUIT

PART NO.: SEE SHEET 2

DRAWING NUMBER: M02947YB-DC

DRAWN BY	DATE	CHK	SCALE	SIZE
SAT	06-26-18	PJI	NONE	A

SHT 1 OF 2

Downloaded from Arrow.com.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

UNIVERSAL 12F - CASSETTE			
PANDUIT PART NUMBER	FIBER TYPE	PERFORMANCE LEVEL	ADAPTER COLOR (SPLIT SLEEVE)
FQXN-12-10U	OM3	STANDARD LOSS	AQUA (ZIRCONIA)
FQZN-12-10U	OM4		
FQ9N-12-10U	OS2		BLUE (ZIRCONIA)
FQ9N-12-LAU	OS1/OS2		APC GREEN (ZIRCONIA)
FQXO-12-10U	OM3	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQZO-12-10U	OM4		
FQWO-12-10U	OM5		LIME GREEN (ZIRCONIA
FQXA-12-10U	OM3	ULTRA LOW LOSS	AQUA (ZIRCONIA)
FQZA-12-10U	OM4		
FQSA-12-10U	OM4+		
FQWA-12-10U	OM5		LIME GREEN (ZIRCONIA

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
					REFER TO SHEET 1 FOR REVISION HISTORY	

TITLE

QUICKNET SFQ CASSETTE, 12 FIBER DUPLEX LC TO MPO CASSETTE METHOD U [UNIVERSAL]

CUSTOMER DRAWING

ITEM REVISION NAME: M02947YB/01

DATASET FILE NAME: M02947YB_DC/01C

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .XXX ± .010 [0.3]

.XX ± .03 [0.8] ANGLES ±

THIRD ANGLE PROJECTION

PANDUIT

PART NO.: SEE TABLE

DRAWING NUMBER: M02947YB-DC

DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	SIZE
SAT	06-26-18	PJI	NONE		A

Downloaded from Arrow.com.