
Part Number : 2037023100
Product Description : FineAdjust Applicator for Nano-Fit Wire-to-Wire Plug Terminals, 26-24 AWG, UL 1061 Wire
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037023100-000.pdf

TM-638000029-001.pdf

TM-638004900-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Nano-Fit Wire-to-Wire Plug Terminals, 26-24 AWG, UL 1061 Wire
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Nano-Fit
Tool Type	Applicator
UPC	193264498734
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where

Downloaded from Arrow.com.

	Molex Tooling is modified.

Applicable Parts

Description	Part Number
Nano-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 26-24 AWG	2014471200
Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, 26-24 AWG	2014471300
Nano-Fit Crimp Terminal, Male, 2.54µm Matte Tin Plating, Lubricated, 26-24 AWG	2014471400
Nano-Fit Crimp Terminal, Male, 0.76µm Gold (Au) Plating, Lubricated, 26-24 AWG	2014471600

Downloaded from Arrow.com.