

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1462200300](#)
Status: **Active**
Overview: [Internet of Things \(IoT\) Antennas: Wi-Fi, Bluetooth, Zigbee](#)
Description: [Wi-Fi 6E+GNSS PCB Cabled Balanced Antenna, 16.60mm Width, 300.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors](#)

Documents:

3D Model	Application Specification AS-146220-100-001 (PDF)
3D Model (PDF)	Packaging Specification PK-146220-100-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-146220-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Antennas
Series	146220
Component Type	PCB Antenna with Cable
Function	Signal
Mates With	734120110 Microcoaxial RF, 50 Ohm
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz GPS-Wi-Fi Antenna
Protocol	BeiDou, BLE, BT, Galileo, GLONASS, GPS, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Combo Wi-Fi/GNSS Antenna
UPC	889056569705

Physical

Cable Length	300.00mm
Length	53.50mm
Mounting Style	Screw-Nut
Net Weight	2.395/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.81mm
Width	16.60mm


Electrical

Band#1 F_End (MHz)	1602
Band#1 F_Start (MHz)	1575.42
Band#2 F_End (MHz)	2483.5
Band#2 F_Start (MHz)	2400
Band#3 F_End (MHz)	5850
Band#3 F_Start (MHz)	5150
Band#4 F_End (MHz)	6000
Band#4 F_Start (MHz)	3000
Electrical Connectivity	Cable
Peak Gain (dBi)	1.8 @ 1575 MHz, 2.3 @ 2.4 GHz, 2.5 @ 3 GHz, 2.8 @ 5 GHz
Return Loss - S11 (dB)	< -8
Total Efficiency	>61% @ 3 GHz, >65% @ 5 GHz, >68% @ 2.4 GHz, >70% @ 1575 MHz

Material Info

Reference - Drawing Numbers

Application Specification	AS-146220-100-001
Packaging Specification	PK-146220-100-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[146220](#) Series

This document was generated on 03/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION